

Technical Advisory Bulletin

Date: January 6, 2006 **Number:** TAB 06-001

To: Distribution, Global

DLS2002 Serial Port USB Compatibility Chart

In cases where the downloading computer does not support a dedicated serial COM Port, a USB to Serial converter is required for MD-12 and/or PC-Link operation. The following is a chart of USB devices and functions that they have been found to be compatible with (results may vary depending on computer configuration).

| USB Device | MD-12 Outgoing Call | MD-12 Incoming Call | PC-Link 9600 Baud |
|------------------|----------------------------|---------------------------|---------------------|
| | | | |
| Keyspan | All panels function | All panels function | All panels function |
| USA-19HS | | · | • |
| IO Gear - UC232A | Maxsys – Yes | No | All panels function |
| | Power – Yes | | |
| | Classic – No | | |
| IONETWORKS - | Maxsys – No | No | All panels function |
| Edgeport1 USB | Power – No | | |
| | Classic – Yes | | |
| Belkin - F5U103 | Maxsys – No | Maxsys – Yes | All panels function |
| | Power – No | Power – No | |
| | Classic - Yes | Classic - Yes | |
| | | | |
| | | NOTE: DLS callback may be | |
| | | difficult to perform. | |
| QVS – UR2000M | Maxsys – Yes | Maxsys – No | All panels function |
| | Power – Yes | Classic – No | |
| | Classic – No | Power - Yes | |
| | NOTE: Or many mile atticus | | |
| | NOTE: Communication | | |
| | errors can occur on some | | |
| | operating systems. | | |

Please contact the DSC Customer Help Center at 905-760-3000, or send an email to info@dsc.com or tech@dsc.com if you have any questions.

Harry Scholz Manager, Customer Help Center

905-760-3000 ext. 2441 hscholz@dsc.com

